


EasyClick 200



















Interflex Polska Sp. z o.o.


62-025 Kostrzyn Wlkp., tel: (61) 817 86 03 fax:(61) 817 86 26

www.interflex.pl


e-mail: biuro@interflex.pl




x2



x2




x2




10x60



8x60




8/18






Typ	N	BB
EasyClick 200	200	100

EasyClick 200











OPTION



EasyClick 200




IM-15-200-05-0


EasyClick 200 L+R





EasyClick 200










EasyClick 200

H<2520

B<3000

L+R




PL czerwony
GB red
D rot
NL root
SK cerveny

PL czerwony
GB red
D rot
NL root
SK cerveny



PL czarny
GB black
D schwarz
NL zwart
SK cierny

PL czarny
GB black
D schwarz
NL zwart
SK cierny







EasyClick 200


H>2520

B>3000

L+R





RiL




- | | | | |
|----|----------|----|----------|
| PL | czerwony | PL | czerwony |
| GB | red | GB | red |
| D | rot | D | rot |
| NL | root | NL | root |
| SK | cerveny | SK | cerveny |





- | | | | |
|----|---------|----|---------|
| PL | czarny | PL | czarny |
| GB | black | GB | black |
| D | schwarz | D | schwarz |
| NL | zwart | NL | zwart |
| SK | cierny | SK | cierny |









EasyClick 200



EasyClick 200

M MOTOR 
HAND 






EasyClick 200

OPTION

4800 < B < 5000




2-3 Ω





OPTION

B > 5000


2-5 Ω




EasyClick 200



EasyClick 200



Z x 360°






1




L

R



8



RiL


3

4

1

2

7



9

9

